ASAHI KINZOKU Co., Ltd

The pioneer of loading machine.

## **Automatic Folding Device**

# X-ray Inspection Device


equipped

MODEL

)RA-60

High-Speed Storage

Jam and foreign object inspection system is incorporated.



High-speed filling machines compatible.

folded and stored.

Jam and foreign object inspecting with the inspection device function.

> Easy operation with Touch-Panel.




#### ORA-600TK FEATURES

#### Automatic Folding Device X-ray Inspection Device equipped

Can be used for Powder, Liquid, Spices, Desiccants, Oxygen absorbers and more.

#### SCHEMATIC DIAGRAM



### STANDARD SPECIFICATIONS

Storage Speed 60 m/min (When the box length 600mm)

Pouch Size Width 30~100mm Length 30~100mm

Machine Dimensions L2545mm × H2175mm × D770mm(1230mm)

Storage Box Size  $L700mm \times H350mm \times D500mm$  Reserve Box Size  $L1100mm \times H770mm \times D270mm$ 

Air Pressure Consumption 0.4~0.6MPa Air Consumption 160Nl/min

Power Supply Single phase AC 200V 50/60Hz 2.5KVA

Machine Weight 400kg

## OPTIONAL DEVICES ARE AVAILABLE

#### \*Automatic Folding Device oriented in the left direction is also available.

- Please do not hesitate to contact ASAHI KINZOKU for expert advice about our new Automatic Folding Device.
- Specifications and appearance are subject to change without notice. (because of improvements or updates).
- Additions or changes to the specifications can be arranged through consultation.



CAUTION

For Safe Use

- •Read operation manual carefully before use to insure proper and correct operation
- •Use the machine only with indicated electric current and voltage
- •Be sure to ground the machine to prevent electrocution or short circuit.

Sales& Manufacturing Headquarters



505 Simomaruya-cho, Nishi-iru, Chiekoin-dori, Shimodachiuri-dori, Kamigyo-ku, Kyoto city 602 - 8176 JAPAN

Tel +81-75-801-0154 Fax +81-75-842-1351

URL http://www.akg.jp/kinzoku/

E-mail asahi@akg.jp

**Tokyo Sales Office** 

10-2 Miyamoto-cho, Ageo city, Saitama Prefecture 362-0036 JAPAN

Tel +81-48-771-0662 Fax +81-48-773-5937

**Kyushu Sales Office** 

No. 206 Ichikura Building, 1-26, 2-chome, Hakata station south, Hakata-ku, Fukuoka city 812-0016, JAPAN

Tel +81-92-471-5234 Fax +81-92-473-7150

■ Reference